



Nitric Oxide (NO)

MIDAS-S-NOX

MIDAS-E-NOX


Nitric Oxide (NO)

MIDAS-S-NOX

MIDAS-E-NOX



Midas® sensor cartridges are intended for use only with Honeywell Analytics' Midas® gas detector system. Please refer to the Midas® Technical Manual for further details.



| Gas Measured | Nitric Oxide (NO) |
|--|--|
| Cartridge Part Number | MIDAS-S-NOX 1 year standard warranty MIDAS-E-NOX 2 year extended warranty |
| Sensor Technology | 3 electrode electrochemical cell |
| Measuring Range (ppm) | NO 0 – 100ppm |
| Minimum Alarm 1 Set Point | 12.5ppm |
| Lower Detectable Limit (LDL) | 9.0ppm |
| Repeatability | < ± 2% of measured value |
| Linearity | < ± 5% of measured value |
| Response Time $t_{92.5}$ | < 15 seconds |
| Sensor Cartridge Life Expectancy | ≥ 24 months under typical application conditions |
| Operating Temperature | 0°C to +40°C (32°F to 104°F) |
| Effect of Temperature | < ± 0.09ppm / °C (0°C to 30°C) < ± 0.17ppm / °C (30°C to 40°C) |
| Zero Sensitivity | < ± 0.5% of measured value / °C |
| Operating Humidity (continuous) | 15 – 90% rH |
| Effect of Humidity | No effect |
| Zero Sensitivity | < ± 0.5% of measured value / % rH |
| Operating Pressure | 90 – 110kPa |
| Effect of Position | No effect in typical application |
| Long Term Drift | No drift |
| Zero Sensitivity | < 2% of measured value / month |
| Calibration Gas | Nitric Oxide (NO) |
| Challenge Gas (Bump Test) | Nitric Oxide (NO) |
| Warm Up Time | < 10 minutes |
| Storage Temperature | +5°C to +25°C (+41°F to +77°F) |

The sensor data listed is based on ideal test environment; observed performance may vary based on the actual monitoring system and the sampling conditions employed

General Specification



Midas® is a registered trademark of Honeywell Analytics.

As with all electrochemical sensor cells, dramatic output changes in reported concentrations can be expected under rapidly changing environmental conditions. Please ensure sensors are located in areas not prone to sudden changes in humidity and temperature.

Actual readings may be affected by flow rates (although Midas® automatically controls flow rates within specified ranges) and absorption on tubing and other gas path surfaces.

All sensors are shipped pre-calibrated to traceable national standards. Dependent on actual operating conditions and overall exposure to gases, each sensor may not require in-field calibration for up to 24 months subject to any requirements to calibrate from local regulations or site practices.

Calibration and challenge gases should be from a certified and reliable source.

Cross Sensitivities

Each Midas® sensor is potentially cross sensitive to other gases and this may cause a gas reading when exposed to other gases than those originally designated. The table below presents typical readings that will be observed when a new sensor cartridge is exposed to the cross sensitive gas (or a mixture of gases containing the cross sensitive species).

| Gas / Vapour | Chemical Formula | Concentration Applied (ppm) | Reading (ppm NO) |
|-------------------|------------------|-----------------------------|------------------|
| Carbon Monoxide | CO | 300 | 0 |
| Hydrogen Sulphide | H ₂ S | 15 | 1.5 |
| Nitrogen Dioxide | NO ₂ | 5 | < 1.5 |
| Sulphur Dioxide | SO ₂ | 5 | 0 |

Our Product Range



Fixed Gas Monitoring

Honeywell Analytics offers a wide range of fixed gas detection solutions for a diverse array of industries and applications including: Commercial properties, industrial applications, semiconductor manufacturers, energy plants and petrochemical sites.

- » Detection of flammable, oxygen and toxic gases (including exotics)
- » Innovative use of 4 core sensing technologies – paper tape, electrochemical cell, catalytic bead and infrared
- » Capability to detect down to Parts Per Billion (ppb) or Percent by Volume (%v/v)
- » Cost effective regulatory compliance solutions

Portable Gas Monitoring

When it comes to personal protection from gas hazards, Honeywell Analytics has a wide range of reliable solutions ideally suited for use in confined or enclosed spaces.

These include:

- » Detection of flammable, oxygen and toxic gases
- » Single gas personal monitors – worn by the individual
- » Multi-gas portable gas monitors – used for confined space entry and regulatory compliance
- » Multi-gas transportable monitors – used for temporary protection of area during site construction and maintenance activities

Technical Services

At Honeywell Analytics, we believe in the value of great service and customer care. Our key commitment is providing complete and total customer satisfaction. Here are just a few of the services we can offer:

- » Full technical support
- » Expert team on hand to answer questions and queries
- » Fully equipped workshops to ensure quick turnaround on repairs
- » Comprehensive service engineer network
- » Training on product use and maintenance
- » Mobile calibration service
- » Customised programmes of preventative/corrective maintenance
- » Extended warranties on products

Find out more

www.honeywellanalytics.com

Contact Honeywell Analytics:

Europe, Middle East, Africa

Life Safety Distribution AG
Wilstrasse 11-U31
CH-8610 Uster
Switzerland
Tel: +41 (0)44 943 4300
Fax: +41 (0)44 943 4398
gasdetection@honeywell.com

Americas

Honeywell Analytics Distribution, Inc.
405 Barclay Blvd.
Lincolnshire, IL 60069
USA
Tel: +1 847 955 8200
Toll free: +1 800 538 0363
Fax: +1 847 955 8208
detectgas@honeywell.com

Asia Pacific

Honeywell Analytics Asia Pacific
#508, Kolon Science Valley (1)
187-10 Guro-Dong, Guro-Gu
Seoul, 152-050,
Korea
Tel: +82 (0)2 2025 0307
Fax: +82 (0)2 2025 0329
analytics.ap@honeywell.com

Technical Services

ha.emea.service@honeywell.com

www.honeywell.com

Please Note:

While every effort has been made to ensure accuracy in this publication, no responsibility can be accepted for errors or omissions. Data may change, as well as legislation, and you are strongly advised to obtain copies of the most recently issued regulations, standards, and guidelines. This publication is not intended to form the basis of a contract.